



# SmartBright Panel

## RC099V LED36S/865 W60L60 GM

SmartBright Panel, 865 cool daylight

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	CE mark
ENEC mark	-

Light Technical	
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Number of light sources	12
Light source color	865 cool daylight
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	110° x 110°

Operating and Electrical	
Input Voltage	220-240 V
Power Consumption	34 W
Power Factor (Fraction)	0.9

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Housing Color	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RC099V LED36S/865 W60L60 GM


# SmartBright Panel

Full product name	RC099V LED36S/865 W60L60 GM
Full product code	911401835299
Order code	911401835299
Material Nr. (12NC)	911401835299


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED36S W60x60 GH	597x297x15
RC099V LED36S W60x120 GH	1194x297x15
RC099V LED36S W60x60 SUS GH	603x603x15
RC099V LED36S W60x120 SUS GH	1206x603x15
RC099V LED36S W60x60 PCV GH	603x603x15
RC099V LED36S W60x120 PCV GH	1206x603x15
RC099V LED36S W60x60 GH	597x297x15
RC099V LED36S W60x120 GH	1194x297x15
RC099V LED36S W60x60 SUS GH	603x603x15
RC099V LED36S W60x120 SUS GH	1206x603x15
RC099V LED36S W60x60 PCV GH	603x603x15
RC099V LED36S W60x120 PCV GH	1206x603x15



RC099V LED36S W60x60 GH  
RC099V LED36S W60x120 SUS GH  
RC099V LED36S W60x60 PCV GH  
RC099V LED36S W60x120 PCV GH



RC099V LED36S W60x120 GH  
RC099V LED36S W60x120 SUS GH  
RC099V LED36S W60x120 PCV GH  
RC099V LED36S W60x120 SUS GH  
RC099V LED36S W60x120 PCV GH

