



SmartBright Panel

RC099V LED36S/865 W60L60 SUS GM

SmartBright Panel, 865 cool daylight

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
CE mark	CE mark
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Number of light sources	12
Light source color	865 cool daylight
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	110° x 110°
Operating and Electrical	
Input Voltage	220-240 V
Power Consumption	34 W
Power Factor (Fraction)	0.9

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes
Mechanical and Housing	
Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC099V LED36S/865 W60L60 SUS GM


SmartBright Panel

Full product name	RC099V LED36S/865 W6L60 SUS GM
Full product code	911401835699
Order code	01835699
Material Nr. (12NC)	911401835699


Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED36S W6xL60 GH	597x297x7,5
RC099V LED36S W6xL120 GH	1197x297x7,5
RC099V LED36S W6xL60 SUS GH	603x463x7,5
RC099V LED36S W6xL120 SUS GH	1203x463x7,5
RC099V LED36S W6xL60 PCV GH	603x463x7,5
RC099V LED36S W6xL120 PCV GH	1203x463x7,5
RC099V LED36S W6xL60 GH	597x297x7,5
RC099V LED36S W6xL120 GH	1197x297x7,5
RC099V LED36S W6xL60 SUS GH	603x463x7,5
RC099V LED36S W6xL120 SUS GH	1203x463x7,5
RC099V LED36S W6xL60 PCV GH	603x463x7,5
RC099V LED36S W6xL120 PCV GH	1203x463x7,5




RC099V LED36S W6xL60 GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL60 PCV GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL60 PCV GH




RC099V LED36S W6xL120 GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL120 PCV GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL120 PCV GH

Product Type	Size LxWxH(mm)
RC099V LED36S W6xL60 GH	597x297x7,5
RC099V LED36S W6xL120 GH	1197x297x7,5
RC099V LED36S W6xL60 SUS GH	603x463x7,5
RC099V LED36S W6xL120 SUS GH	1203x463x7,5
RC099V LED36S W6xL60 PCV GH	603x463x7,5
RC099V LED36S W6xL120 PCV GH	1203x463x7,5
RC099V LED36S W6xL60 GH	597x297x7,5
RC099V LED36S W6xL120 GH	1197x297x7,5
RC099V LED36S W6xL60 SUS GH	603x463x7,5
RC099V LED36S W6xL120 SUS GH	1203x463x7,5
RC099V LED36S W6xL60 PCV GH	603x463x7,5
RC099V LED36S W6xL120 PCV GH	1203x463x7,5



RC099V LED36S W6xL60 GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL60 PCV GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL60 PCV GH



RC099V LED36S W6xL120 GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL120 PCV GH
RC099V LED36S W6xL120 SUS GH
RC099V LED36S W6xL120 PCV GH

