



SmartBright Panel

RC099V LED36S/840 W30L120 SUS GM

SmartBright Panel, 840 neutral white

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data

General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Number of gear units	1 unit	Driver/power unit/transformer	Power supply unit (On/Off)
Driver included	Yes	Constant light output	Yes
Glow-wire test	Temperature 650 °C, duration 30 s	Mechanical and Housing	
CE mark	CE mark	Housing Material	Steel
ENEC mark	-	Reflector material	Steel
Light Technical		Optic material	Polycarbonate
Correlated Color Temperature (Nom)	4000 K	Housing Color	White
Color rendering index (CRI)	80	Approval and Application	
Number of light sources	12	Ingress protection code	IP20 [Finger-protected]
Light source color	840 neutral white	Mech. impact protection code	IK02 [0.2 J standard]
Optic type	Beam angle 60 to 120°	Protection class IEC	Safety class I
Optical cover type	Transparent bowl with white cover	Initial Performance (IEC Compliant)	
Luminaire light beam spread	110° x 110°	Luminous flux tolerance	+/-10%
Operating and Electrical		Power consumption tolerance	+/-10%
Input Voltage	220-240 V	Product Data	
Power Consumption	34 W	Order product name	RC099V LED36S/840 W30L120 SUS GM
Power Factor (Fraction)	0.9		

Full product name	RC099V LED36S/840 W30L120 SUS GM
Full product code	911401835799
Order code	911401835799
Material Nr. (12NC)	911401835799

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

