



SmartBright Panel

RC099V LED36S/865 W60L60 PCV GM

SmartBright Panel, 865 cool daylight

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data

General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Number of gear units	1 unit	Driver/power unit/transformer	Power supply unit (On/Off)
Driver included	Yes	Constant light output	Yes
CE mark	CE mark		
ENEC mark	-	Mechanical and Housing	
Glow-wire test	Temperature 650 °C, duration 30 s	Housing Material	Steel
		Reflector material	Steel
Light Technical		Optic material	Polycarbonate
Correlated Color Temperature (Nom)	6500 K	Housing Color	White
Color rendering index (CRI)	80		
Number of light sources	12	Approval and Application	
Light source color	865 cool daylight	Ingress protection code	IP20 [Finger-protected]
Optic type	Beam angle 60 to 120°	Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Transparent bowl with white cover	Protection class IEC	Safety class I
Luminaire light beam spread	110° x 110°		
Operating and Electrical		Initial Performance (IEC Compliant)	
Input Voltage	220-240 V	Luminous flux tolerance	+/-10%
Power Consumption	34 W	Power consumption tolerance	+/-10%
Power Factor (Fraction)	0.9		
		Product Data	
		Order product name	RC099V LED36S/865 W60L60 PCV GM

Full product name	RC099V LED36S/865 W60L60 PCV GM
Full product code	911401836099
Order code	01836099
Material Nr. (12NC)	911401836099

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

