



OneSpace luminous ceiling prefab

LP710P ONESPACE PREFAB L2860W1733 4000K

OneSpace luminous ceiling prefab panel, length 2860 mm, width 1733 mm, light color 4000 K

Many business customers want a lighting solution that recalls the feeling of natural daylight, creating a calm and peaceful environment. They want great functional lighting that feels as good as it looks. Philips OneSpace luminous ceiling prefab is an impressive ultra-thin and compact standard unit with an excellent uniform light distribution. It also helps improve the acoustics in a room and meets the most stringent fire safety standards. The result is a ceiling unit that produces an amazing light effect while the light source remains hidden from view. With its minimalistic design, this slim, compact unit will blend in perfectly with any interior.

Product data

General Information			
Number of light sources	1 [1 pc]	CE mark	CE mark
Light source colour	840 neutral white	ENEC mark	ENEC mark
Light source replaceable	No	UL mark	UL mark
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Unified glare rating CEN	Not applicable
Driver included	Yes	Operating and Electrical	
Connection	SI [Screw connection block]	Input voltage	220 to 240 V
Protection class IEC	Safety class I (I)	Input frequency	50 to 60 Hz
Ready-to-install	Ready-to-install	Control signal voltage	0-16 V DC DALI
Flammability mark	NO [-]	Controls and Dimming	
Type description	ONESPACE PREFAB L2860W1733 4000K [OneSpace luminous ceiling prefab panel, length 2860 mm, width 1733 mm, light color 4000 K]	Dimmable	Yes

OneSpace luminous ceiling prefab

Mechanical and Housing

Housing material	Aluminum
Gear tray material	Steel
Colour	Black

Approval and Application

Ingress protection code	IP00 [No protection]
Mech. impact protection code	IK00 [No protection]

Initial Performance (IEC Compliant)

Initial luminous flux	12500 lm
Initial LED luminaire efficacy	66 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	>85
Initial input power	190 W
Power consumption tolerance	+/-10%

Application Conditions

Ambient temperature range	+5 to +35 °C
Maximum dimming level	10%
Suitable for random switching	No

Product Data

Full product code	871869607036999
Order product name	LP710P ONESPACE PREFAB L2860W1733 4000K
EAN/UPC – product	8718696070369
Order code	07036999
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	9120000000417
Net weight (piece)	54.000 kg

