



# CitySphere

## BDP781 GRN30/740 PSD DM CL DGR D9 60P

CITYSPHERE, LED GreenLine 3000 lm, Distribution medium,  
Post-top for diameter 60 mm

At a time of rapidly changing social practices, every city is looking to be more attractive, welcoming, convenient and safe. CitySphere is a post-top ambiance LED luminaire designed to create a comfortable and pleasant atmosphere that puts the users of public spaces at ease. A slim, discreet presence during the day, it brings urban spaces to life at night. CitySphere delivers a visually comfortable volume of light and gives the city its own color signature. CitySphere comes with dedicated spigots, brackets and poles, enabling development planners, specifiers and decision makers to create a consistent urban identity and ambience.

### Product data

General Information		Value ladder	Specification
Lamp family code	GRN30 [LED GreenLine 3000 lm]	Embedded control	-
Light source replaceable	No	CE mark	Yes
Number of gear units	1 unit	Warranty period	3 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Photocell	-	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BDP781 [CITYSPHERE]	Light Technical	
Lighting Technology	LED	Upward light output ratio	0.03
		Luminous Flux	2,454 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	148° x 88°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	0.15 ms
Power Consumption	26 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	Cable 1.8 m without plug
Number of products on MCB of 16 A type B	11

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Conical
Optical cover finish	Clear
Overall height	172 mm

Overall diameter	661 mm
Effective projected area	0.343 m²

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

#### Product Data

Order product name	BDP781 GRN30/740 PSD DM CL DGR D9 60P
Full product name	BDP781 GRN30/740 PSD DM CL DGR D9 60P
Full product code	871794317626700
Order code	912300022672
Material Nr. (12NC)	912300022672
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943176267
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943176267

Dimensional drawing

