



CitySphere

BDP781 ECO50/740 PSD DM CL DGR D9 60P

CITYSPHERE, LED EconomyLine 5000 lm, Distribution medium, Post-top for diameter 60 mm

At a time of rapidly changing social practices, every city is looking to be more attractive, welcoming, convenient and safe. CitySphere is a post-top ambiance LED luminaire designed to create a comfortable and pleasant atmosphere that puts the users of public spaces at ease. A slim, discreet presence during the day, it brings urban spaces to life at night. CitySphere delivers a visually comfortable volume of light and gives the city its own color signature. CitySphere comes with dedicated spigots, brackets and poles, enabling development planners, specifiers and decision makers to create a consistent urban identity and ambience.

Product data

General Information		Value ladder	Specification
Lamp family code	ECO50 [LED EconomyLine 5000 lm]	Embedded control	-
Light source replaceable	No	CE mark	Yes
Number of gear units	1 unit	Warranty period	3 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Photocell	-	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BDP781 [CITYSPHERE]	Light Technical	
Lighting Technology	LED	Upward light output ratio	0.03
		Luminous Flux	4,090 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	148° x 88°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	0.15 ms
Power Consumption	44 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	Cable 1.8 m without plug
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Conical
Optical cover finish	Clear
Overall height	172 mm

Overall diameter	661 mm
Effective projected area	0.343 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BDP781 ECO50/740 PSD DM CL DGR D9 60P
Full product name	BDP781 ECO50/740 PSD DM CL DGR D9 60P
Full product code	871794317628100
Order code	17628100
Material Nr. (12NC)	912300022674
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943176281
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943176281

Dimensional drawing

