



# CitySphere

## BDP780 GRN60/830/RD PSU DS RB DGR CLO 60

CitySphere, LED GreenLine 6000 lm, Distribution symmetrical, Constant light output, Post-top for diameter 60 mm

At a time of rapidly changing social practices, every city is looking to be more attractive, welcoming, convenient and safe. CitySphere is a post-top ambiance LED luminaire designed to create a comfortable and pleasant atmosphere that puts the users of public spaces at ease. A slim, discreet presence during the day, it brings urban spaces to life at night. CitySphere delivers a visually comfortable volume of light and gives the city its own color signature. CitySphere comes with dedicated spigots, brackets and poles, enabling development planners, specifiers and decision makers to create a consistent urban identity and ambience.

### Product data

General Information		Value ladder		Specification	
Lamp family code	GRN60 [LED GreenLine 6000 lm]	Embedded control		Constant light output	
Light source replaceable	No	CE mark		Yes	
Number of gear units	2 units	Warranty period		3 years	
Driver included	Yes	Flammability mark		For mounting on normally flammable surfaces	
Photocell	-	ENEC mark		ENEC mark	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test		Temperature 650 °C, duration 5 s	
Light source engine type	LED	EU RoHS compliant		Yes	
Product family code	BDP780 [CitySphere]	Light Technical			
Lighting Technology	LED	Upward light output ratio		0.03	
		Luminous Flux		4,590 lm	
		Standard tilt angle posttop		0°	
		Standard tilt angle side entry		0°	

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	80
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	148° x 148°
Optic type outdoor	Distribution symmetrical

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	44 W
Average CLO power consumption	49.5 W
End CLO power consumption	55 W
Inrush current	70 A
Inrush time	0.19 ms
Power Consumption	55 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 1.8 m without plug
Number of products on MCB of 16 A type B	9

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Conical

Optical cover finish	Ribbed
Overall height	662 mm
Overall diameter	661 mm
Effective projected area	0.343 m²

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.410, 0.390) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

#### Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

#### Product Data

Order product name	BDP780 GRN60/830/RD PSU DS RB DGR CLO 60
Full product name	BDP780 GRN60/830/RD PSU DS RB DGR CLO 60
Full product code	871794317635900
Order code	912300022681
Material Nr. (12NC)	912300022681
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943176359
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943176359

Dimensional drawing

