



FlowLine

BGB330 3K/NW SH DTA-WB C500C

FLOWLINE, Distribution tunnel asymmetrical wide beam

Tunnels often require a linear interior lighting solution. FlowLine offers an LED solution where traditionally fluorescent lighting was used. FlowLine outperforms fluorescent lighting over the full life cycle in terms of cost, safety and performance, and is a competitive alternative to HPS point-source interior lighting on total cost of ownership. Its linear build allows continuous or spaced line lighting schemes, providing optimal guidance and a high level of visual comfort. Performance can be further optimized by using FlowLine in combination with our dedicated lighting controls and service packages.

Product data

General Information		EU RoHS compliant		Yes
Lamp family code	ECO [LED EconomyLine]			
Light source replaceable	No	Light Technical		
Number of gear units	Unit	Upwards light output ratio	0	
Driver included	No	Luminous Flux	3,311 lm	
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Standard tilt angle post-top	0°	
Light source engine type	LED	Standard tilt angle side entry	0°	
Product family code	BGB330 [FLOWLINE]	Correlated Colour Temperature	4000 K	
Lighting Technology	LED	Luminous efficacy (rated) (nom.)	118 lm/W	
CE mark	Yes	Colour rendering index (CRI)	≥70	
Warranty period	5 years	Light source colour	Neutral white	
Flammability mark	For mounting on normally flammable surfaces	Optical cover type	Tempered glass	
ENEC mark	ENEC mark	Luminaire light beam spread	25° - 4° x 150°	
		Optic type outdoor	Distribution tunnel asymmetrical wide beam	
		Operating and Electrical		
		Input Voltage	34.3 V	

Line Frequency	0 Hz
Inrush current	0 A
Inrush time	0 ms
Power Consumption	28.1 W
Power Factor (Fraction)	0.97
Connection	External connector
Cable	Cable 0.5 m with cable connector
Number of products on MCB of 16 A type B 1	

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Constant light output	No

Mechanical and Housing

Housing material	High-grade stainless steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Housing Colour	Steel
Mounting device	-
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	1,591 mm
Overall width	210 mm
Overall height	48 mm

Dimensional drawing



Effective projected area	0.009 m²
Dimensions (height x width x depth)	48 x 210 x 1591 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.377, 0.373) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0 %
------------------------------------	-----

Product Data

Order product name	BGB330 3K/NW SH DTA-WB C500C
Full product name	BGB330 3K/NW SH DTA-WB C500C
Full EOC	871794318326500
Order code	18326500
Material no. (12 NC)	912300022964
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8717943183265
Numerator – packs per outer box	1
EAN/UPC – Case	8717943183265

