



# CitySphere

## BDP782 GRN20/740 PSD DS CL GR D9 60P

CITYSPHERE, LED GreenLine 2000 lm, LED, 740 neutral white, Power supply unit with DALI interface, 220 to 240 V, 50 to 60 Hz, Safety class I, Distribution symmetrical, Polycarbonate bowl/cover UV-resistant, Grey, Philips standard surge protection level, Cable 1.8 m without plug, Post-top for diameter 60 mm

At a time of rapidly changing social practices, every city is looking to be more attractive, welcoming, convenient and safe. CitySphere is a post-top ambiance LED luminaire designed to create a comfortable and pleasant atmosphere that puts the users of public spaces at ease. A slim, discreet presence during the day, it brings urban spaces to life at night. CitySphere delivers a visually comfortable volume of light and gives the city its own color signature. CitySphere comes with dedicated spigots, brackets and poles, enabling development planners, specifiers and decision makers to create a consistent urban identity and ambience.

### Product data

General Information			
Lamp family code	GRN20 [LED GreenLine 2000 lm]		B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	No	Light source engine type	LED
Number of gear units	1 unit	Product family code	BDP782 [CITYSPHERE]
Driver included	Yes	Lighting Technology	LED
Photocell	-	Value ladder	Specification
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	Embedded control	-
		CE mark	Yes
		Warranty period	3 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark

Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

#### Light Technical

Upward light output ratio	0.03
Luminous Flux	1,588 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	148° x 148°
Optic type outdoor	Distribution symmetrical

#### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	65 A
Inrush time	0.1 ms
Power Consumption	18 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	Cable 1.8 m without plug
Number of products on MCB of 16 A type B	21

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum

Housing Color	Grey
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Conical
Optical cover finish	Clear
Overall height	172 mm
Overall diameter	661 mm
Effective projected area	0.343 m²

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

#### Product Data

Order product name	BDP782 GRN20/740 PSD DS CL GR D9 60P
Full product name	BDP782 GRN20/740 PSD DS CL GR D9 60P
Full product code	871794321411200
Order code	912300023267
Material Nr. (12NC)	912300023267
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943214112
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943214112

