



TubeLine

BGP360 LED60/740 II DTS CFW C250W GP

TubeLine 2M, LED module 6000 lm, Distribution tunnel symmetrical, Safety class II, Cord with plug Wieland/Adels compatible 3-pole

For customers who demand a high level of visual comfort from their tunnel luminaires, fluorescent linear lighting has traditionally been the preferred choice. With excellent light uniformity on the road and walls, perfect visual guidance and high color rendering, linear lighting offers drivers superior lighting quality and safety. It also promises high system redundancy compared to point source lighting solutions. With Philips TubeLine tunnel luminaires, you can achieve the same lighting quality, but with all the added advantages of LED technology. TubeLine is a state-of-the-art tunnel luminaire that harnesses the latest LED technology with optimized dimensions and attractive pricing for a quick return on investment. Linear lighting has never been more achievable for tunnel lighting and underpass lighting on a limited budget.

Product data

General Information		
Lamp family code	LED60 [LED module 6000 lm]	B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source replaceable	No	
Number of gear units	1 unit	
Gear	-	
Driver included	No	
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires - January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example	

Light source engine type	LED
Product family code	BGP360 [TubeLine 2M]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	3 years

Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	5,400 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color rendering index (CRI)	≥80
Number of light sources	48
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150°
Optic type outdoor	Distribution tunnel symmetrical

Operating and Electrical

Input Voltage	- V
Line Frequency	0 Hz
Inrush current	0 A
Inrush time	0 ms
Power Consumption	35.5 W
Power Factor (Fraction)	0.96
Connection	Flying leads/wires
Cable	Cord with plug Wieland/Adels compatible 3-pole
Number of products on MCB of 16 A type B 11	

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Aluminum

Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	1,998 mm
Overall width	109 mm
Overall height	47 mm
Effective projected area	0.15728 m²
Dimensions (Height x Width x Depth)	47 x 109 x 1998 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.433, 0.403) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L98

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BGP360 LED60/740 II DTS CFW C250W GP
Full product name	BGP360 LED60/740 II DTS CFW C250W GP
Full product code	871869909435500
Order code	09435500
Material Nr. (12NC)	912300023656
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699094355
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699094355

Dimensional drawing

