



Coreline tempo large

BVP130 LED80-4S/740 A

Coreline tempo large, 4000 K, Optiflux asymmetrical axis angle 52°, IP66

CoreLine tempo large delivers on the CoreLine promise of innovative, easy to use and high quality luminaires. A narrow range of options makes it easy to find the best lux-for-lux replacement for 150W, 250W, and 400W HID lamps. The CoreLine tempo large floodlighting range offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. The installation is made easy thanks to the U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor areas such as tempo floodlights for industrial/commercial areas, parking lots, etc.

Product data

General Information		Warranty period	
Lamp family code	LED80 [LED module 8000 lm]	Flammability mark	5 years
Light source replaceable	Yes		For mounting on normally flammable surfaces
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver included	Yes	EU RoHS compliant	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Light Technical	
Light source engine type	LED	Upward light output ratio	0
Product family code	BVP130 [CORELINE TEMPO LARGE]	Standard tilt angle posttop	0°
Value ladder	Performance	Standard tilt angle side entry	0°
CE mark	Yes	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	133 lm/W
		Color rendering index (CRI)	>70
		Number of light sources	30
		Light source color	740 neutral white

Coreline tempo large

Optical cover type	Flat glass
Luminaire light beam spread	52° x 102°
Optic type outdoor	Optiflux asymmetrical axis angle 52°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Connection	External connector
Cable	Cable 1.0 m with plug Wieland/Adels compatible 3-pole
Number of products on MCB of 16 A type B 8	

Temperature

Ambient temperature range	-40 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	483 mm
Overall width	422 mm
Overall height	40 mm
Effective projected area	0.15 m²
Dimensions (Height x Width x Depth)	40 x 422 x 483 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.379) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	10 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 75000 h	L80
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BVP130 LED80-4S/740 A
Full product name	BVP130 LED80-4S/740 A
Full product code	871869909724000
Order code	09724000
Material Nr. (12NC)	912300023681
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699097240
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699097240

Coreline tempo large

Dimensional drawing

