



# Coreline tempo large

## BVP130 LED120-4S/740 S

Coreline tempo large, 93 W, 12000 lm, 4000 K, Symmetrical, IP66

CoreLine tempo large delivers on the CoreLine promise of innovative, easy to use and high quality luminaires. A narrow range of options makes it easy to find the best lux-for-lux replacement for 150W, 250W, and 400W HID lamps. The CoreLine tempo large floodlighting range offers lumen packages for many different application areas as well as a choice of high-performance asymmetrical and symmetrical optics. The installation is made easy thanks to the U-shaped universal mounting bracket and the external quick 3-poles connector. It is an ideal solution for outdoor areas such as tempo floodlights for industrial/commercial areas, parking lots, etc.

### Product data

General Information			
Lamp family code	LED120 [LED module 12000 lm]	CE mark	Yes
Light source replaceable	Yes	Warranty period	3 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Light source engine type	LED	Light Technical	
Product family code	BVP130 [CORELINE TEMPO LARGE]	Upward light output ratio	0
Lighting Technology	LED	Luminous Flux	12,000 lm
Value ladder	Performance	Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	129 lm/W
		Color rendering index (CRI)	>70

## Coreline tempo large

Number of light sources	40
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	70° x 21°
Optic type outdoor	Symmetrical

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	93 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cable 0.2 m with cable connector
Number of products on MCB of 16 A type B 1	

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	483 mm
Overall width	365 mm
Overall height	40 mm
Effective projected area	0.15 m²

Dimensions (Height x Width x Depth)	40 x 365 x 483 mm
-------------------------------------	-------------------

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.382, 0.379) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

### Product Data

Order product name	BVP130 LED120-4S/740 S
Full product name	BVP130 LED120-4S/740 S
Full product code	871869909725700
Order code	09725700
Material Nr. (12NC)	912300023682
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699097257
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699097257

## Coreline tempo large

### Dimensional drawing

