



# Micenas LED

## BSP791 LED14-4S/830 II DS50 FG BK

IJM-1, LED module 1400 lm, 830 warm white, Power supply unit (On/Off), Safety class II, Distribution symmetrical 50, Flat glass, Black

Combining contemporary aesthetics and classical inspiration, Micenas LED is an elegant presence in both modern and traditional urban settings. It incorporates the energy-efficient LEDGINE - O engine, ensuring a higher light output over an extended service life and higher energy efficiency. The Eco-designed luminaire has retained its original avant-garde form and provides comfortable ambiance lighting. The housing has a textured black finish that underlines the luminaire's timeless shape, which blends in harmoniously with walls and facades. And a number of dedicated brackets are available, ensuring the decorative integration of luminaire and pole.

### Product data

General Information			
Lamp family code	LED14 [LED module 1400 lm]		might automatically dim down to protect components
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	1 unit	Product family code	BDP791 [IJM-1]
Driver included	Yes	Lighting Technology	LED
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire	Value ladder	Performance
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes

## Micenas LED

<b>Light Technical</b>	
Upward light output ratio	0.03
Luminous Flux	1,126 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	≥80
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	152° x 155°
Optic type outdoor	Distribution symmetrical 50

<b>Operating and Electrical</b>	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	65 A
Inrush time	100 ms
Power Consumption	15 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 2-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	20

<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C

<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

<b>Mechanical and Housing</b>	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Black
Mounting device	Suspension set simple, standard

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	385 mm
Overall width	385 mm
Overall height	561 mm
Effective projected area	0.102 m²
Dimensions (Height x Width x Depth)	561 x 385 x 385 mm

<b>Approval and Application</b>	
Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Protection class IEC	Safety class II

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.433, 0.403) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

<b>Over Time Performance (IEC Compliant)</b>	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L96

<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C

<b>Product Data</b>	
Order product name	BSP791 LED14-4S/830 II DS50 FG BK
Full product name	BSP791 LED14-4S/830 II DS50 FG BK
Full product code	871869910899100
Order code	912300023785
Material Nr. (12NC)	912300023785
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699108991
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699108991

## Micenas LED

### Dimensional drawing

