



ClearFlood Large

BVP651 LED650-4S/740 DX60 ALU PSU

ClearFlood large, LED module 65000 lm, LED, Power supply unit (On/Off), Distribution extra-wide 60, Aluminium

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications. It also includes all the necessary control features and interfaces to make it future-proof and even more efficient. ClearFlood Large lets you choose the exact number of lumens you need for your application. Incorporating extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution offering an outstanding lux/euro ratio and energy savings of up to 40% (without the use of additional controls). The wide choice of optics ensures maximum application coverage. ClearFlood Large is easy to install – you simply plug it in and select the best option for your needs. Perfect for replacing conventional technology and enabling intelligent lighting control while retaining the same electrical installation and poles.

Product data

General Information			
Lamp family code	LED650 [LED module 65000 lm]	luminaire might automatically dim down to protect components	
Light source replaceable	Yes	Light source engine type	LED
Number of gear units	2 units	Product family code	BVP651 [ClearFlood large]
Driver included	Yes	Lighting Technology	LED
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes

ClearFlood Large

Light Technical	
Upwards light output ratio	0
Luminous Flux	58,080 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	143 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	8° - 26° x 82°
Optic type outdoor	Distribution extra-wide 60

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	1.32 ms
Power Consumption	405 W
Power Factor (Fraction)	0.99
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type 3	3
B	

Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	Aluminium
Mounting device	Mounting bracket adjustable
Optical cover/lens shape	Flat

Optical cover/lens finish	Clear
Overall length	817 mm
Overall width	597 mm
Overall height	80 mm
Effective projected area	0.41 m²
Dimensions (height x width x depth)	80 x 597 x 817 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 4 kV differential mode and 4 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Driver failure rate at 5,000 hours	0.005 %
Control gear failure rate at median useful life 100,000 h	0.1 %
Lumen maintenance at median useful life* 100,000 h	L96

Application Conditions	
Performance ambient temperature Tq	25 °C

Product Data	
Order product name	BVP651 LED650-4S/740 DX60 ALU PSU
Full product name	BVP651 LED650-4S/740 DX60 ALU PSU
Full EOC	871869912906400
Order code	12906400
Material no. (12 NC)	912300023965
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718699129064
Numerator – packs per outer box	1
EAN/UPC – Case	8718699129064

ClearFlood Large

Dimensional drawing

