



ClearFlood Large

BVP651 LED700-4S/740 DX60 ALU PSU

ClearFlood large, LED module 70000 lm, LED, Power supply unit (On/Off), Distribution extra wide 60, Aluminum

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications from parking lots to tennis courts. One of the key advantages of ClearFlood Large, is that you can choose the exact lumen rating that you need for your specific application. Because ClearFlood incorporates extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution that offers an outstanding lux/euro ratio and instant energy savings. What’s more, thanks to the wide choice of optics, you will always benefit from maximum coverage for your application. ClearFlood BVP651 is also easy to install – simply plug it in and select the option that best suits your needs.

Product data

General Information			
Lamp family code	LED700 [LED module 70000 lm]	Light source engine type	LED
Light source replaceable	Yes	Service tag	Yes
Number of gear units	2 units	Product family code	BVP651 [ClearFlood large]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires - January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes
		Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver,

ClearFlood Large

	control units, surge protection device, optics, front cover and mechanical parts
--	---

Light Technical

Upward light output ratio	0
Luminous Flux	62,000 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	8° - 26° x 82°
Optic type outdoor	Distribution extra wide 60

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	1.32 ms
Power Consumption	440 W
Power Factor (Fraction)	0.99
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	3

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	880 mm
Overall width	656 mm
Overall height	100 mm
Effective projected area	0.41 m²
Dimensions (Height x Width x Depth)	100 x 656 x 880 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.005 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance at median useful life* 100000 h	L95

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BVP651 LED700-4S/740 DX60 ALU PSU
Full product name	BVP651 LED700-4S/740 DX60 ALU PSU
Full product code	871869912907100
Order code	912300023966
Material Nr. (12NC)	912300023966
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699129071
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699129071

ClearFlood Large

Dimensional drawing

