



1020 Large Classic

Accent, Aluminum Bullyte, Bronze, 150W, PAR 38, 120V

Accent, Aluminum Bullyte, Bronze, 150W, PAR 38, 120V

The Hadco 1020 Bullyte is an excellent choice for accent lighting. Made from die cast aluminum the 1020 has a fully-adjustable swivel arm with vibration-proof locking teeth. Maximum lamping is a 150W PAR38/R40 incandescent lamp.

Product data

General information	
Lamp Envelope Code	A-19
Lamp Source Code	Incandescent
Lamp Watts	150
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No

Operating and electrical	
Voltages	120 V
Luminaire Input Watts	150

Product data	
Order product name	LARGE CLASSIC,120V,150W,PAR38

EAN/UPC - Product	783352002341
Order code	1020-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400104309
Net Weight (Piece)	0.010 kg
Catalog Number	1020-H
Catalog Number Description	Accent, Aluminum Bullyte, Bronze, 150W, PAR 38, 120V