



# BL5016 Micro Accent

## Accent, Aluminum Bullyte w/ Stake, Bulk Pack 25, Bronze, 50W MR16, 12V

Accent, Aluminum Bullyte w/ Stake, Bulk Pack 25, Bronze, 50W MR16, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp; also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

### Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	50
Number of Lamps	1
Mounting	NPT/NPS

  

Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	50

  

Product Data	
Order product name	BULLYTE,12V,50W,W/STAKE,25/CTN

  

EAN/UPC - Product	783352004277
Order code	BL5016-HS725
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400118754
Net Weight (Piece)	0.001 kg
Catalog Number	BL5016-HS725
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Bulk Pack 25, Bronze, 50W MR16, 12V