



# UW1250 Underwater Light

Brass Cord Seal, Brass Friction Ring. 1/2" NPT for use with 16-3 STO-WA entry into junction box.

Brass Cord Seal, Brass Friction Ring. 1/2" NPT for use with 16-3 STO-WA entry into junction box.

The Hadco Underwater luminaires include the UW1250 and UWL1075 fixtures that offer cast bronze construction with a pivoting base. Available in low and line voltage, these luminaires have a natural cast brass finish that will age nicely over time. Optics include a clear convex, tempered glass furnished with silicone O-ring for watertight seal.

## Product data

General Information	
Lamp Watts	50
Mounting	Underwater
Operating and Electrical	
Voltages	120 V
Product Data	
Order product name	NAVAL BRASS CORD SEAL,MALE
Order code	CCH50

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	50
Material Nr. (12NC)	912400120953
Net Weight (Piece)	0.001 kg
Catalog Number	CCH50
Catalog Number Description	Brass Cord Seal, Brass Friction Ring. 1/2" NPT for use with 16-3 STO-WA entry into junction box.