



# CUL16 Copper Accent

## BULLYTE,12V,35W,W/STAKE & LAMP

Accent, Brass Bullyte w/ Stake, Copper, 20W MR16, 12V

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Also available with a Philips MR16 LED lamp.

### Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Quartz	Order code	CUL16S7
Lamp Watts	20	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	15
Mounting	NPT/NPS	Material Nr. (12NC)	912400121604
Operating and Electrical		Net Weight (Piece)	0.010 kg
Voltages	12 V	Commercial Code	CUL16S7
Luminaire Input Watts	20	Catalog Number Description	Accent, Brass Bullyte w/ Stake, Copper, 20W MR16, 12V
Product Data		Quick Ship	Service Smart (2 Days) USA
Order product name	BULLYTE,12V,35W,W/STAKE & LAMP		