



CUL16 Copper Accent

Accent, Brass Bullyte w/ Stake, Copper, 20W MR16, 12V

Accent, Brass Bullyte w/ Stake, Copper, 20W MR16, 12V

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Also available with a Philips MR16 LED lamp.

Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	20
Number of Lamps	1
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	20
Product Data	
Order product name	BULLYTE,12V,35W,W/STAKE & LAMP

EAN/UPC - Product	783352001917
Order code	CUL16S7
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	912400121604
Net Weight (Piece)	0.010 kg
Catalog Number	CUL16S7
Catalog Number Description	Accent, Brass Bullyte w/ Stake, Copper, 20W MR16, 12V