



# DB14 Bollard

**Bollard, Aluminum, Black, 100W INC, 120V, 14"**

Bollard, Aluminum, Black, 100W INC, 120V, 14"

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

## Product data

General information	
Lamp Envelope Code	A-19
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	100

Product data	
Order product name	BLLD,14"RD TOP,120V,100W,A19
EAN/UPC - Product	783352021045
Order code	DB14-A
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121672
Net Weight (Piece)	1.220 kg
Catalog Number	DB14-A
Catalog Number Description	Bollard, Aluminum, Black, 100W INC, 120V, 14"