



# DB14 Bollard

**BLLD,14"RD TOP,120V,100W,A19**

Bollard, Aluminum, Bronze, 100W INC, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

## Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor

  

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100

  

Product Data	
Order product name	BLLD,14"RD TOP,120V,100W,A19

  

EAN/UPC - Product	783352014825
Order code	DB14-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121673
Net Weight (Piece)	7.050 kg
Commercial Code	DB14-H
Catalog Number Description	Bollard, Aluminum, Bronze, 100W INC, 120V
Quick Ship	Service Smart (2 Days) USA