



# DB30 Bollard

## Bollards, Aluminum, Black, 26W CFL, 120V

Bollards, Aluminum, Black, 26W CFL, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

### Product data

<b>General Information</b>		<b>Order code</b>	DB30AA026FE
Lamp Source Code	Compact Fluorescent	Numerator - Quantity Per Pack	1
Lamp Watts	26	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400121712
Mounting	Ground / Floor	Net Weight (Piece)	4.320 kg
<b>Operating and Electrical</b>		Catalog Number	DB30AA026FE
Voltages	120 V	Catalog Number Description	Bollards, Aluminum, Black, 26W CFL, 120V
Luminaire Input Watts	26		
<b>Product Data</b>			
Order product name	BLLD,26W,CFL		