



DB30 Bollard

BLLD,70W MH

Bollards, Aluminum, Black, 70W MH, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		Order code	DB30AA070HE
Lamp Source Code	Metal Halide	Numerator - Quantity Per Pack	1
Lamp Watts	70	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400121717
Mounting	Ground / Floor	Net Weight (Piece)	5.560 kg
Operating and Electrical		Commercial Code	DB30AA070HE
Voltages	120 V	Catalog Number Description	Bollards, Aluminum, Black, 70W MH, 120V
Luminaire Input Watts	70	Quick Ship	-
Product Data			
Order product name	BLLD,70W MH		