



DB30 Bollard

Bollards, Aluminum, Bronze, 26W CFL, 120V

Bollards, Aluminum, Bronze, 26W CFL, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		Order code		DB30HA026FE
Lamp Source Code	Compact Fluorescent	Numerator - Quantity Per Pack	1	
Lamp Watts	26	Numerator - Packs per outer box	1	
Number of Lamps	1	Material Nr. (12NC)	912400121725	
Mounting	Ground / Floor	Net Weight (Piece)	0.010 kg	
Operating and Electrical		Catalog Number	DB30HA026FE	
Voltages	120 V	Catalog Number Description	Bollards, Aluminum, Bronze, 26W CFL, 120V	
Luminaire Input Watts	26			
Product Data				
Order product name	BLLD,26W,CFL			