



DB30 Bollard

Bollards, Aluminum, Bronze, 70W HPS, 120V

Bollards, Aluminum, Bronze, 70W HPS, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information	
Lamp Source Code	High Pressure Sodium
Lamp Watts	70
Number of Lamps	1
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	70
Product Data	
Order product name	BLLD,70W HPS

EAN/UPC - Product	783352022738
Order code	DB30HA070SE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121733
Net Weight (Piece)	0.010 kg
Catalog Number	DB30HA070SE
Catalog Number Description	Bollards, Aluminum, Bronze, 70W HPS, 120V