



# DWC2 Beacon Series

SEMI-RECESSED,120V,20W,T3

Beacon, Composite Semi Recessed, Black, 20W T3, 120V

The DWC series is a low voltage beacon constructed of a single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. It is available in two distinctive heights. Composite is pressure formed, molded-in color. Optical assembly includes a borosilicate glass.

## Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Quartz	Order code	DWC2-A
Lamp Watts	20	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400121907
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120 V	Commercial Code	DWC2-A
Luminaire Input Watts	20	Catalog Number Description	Beacon, Composite Semi Recessed, Black, 20W T3, 120V
Product Data		Quick Ship	-
Order product name	SEMI-RECESSED,120V,20W,T3		