



i15 Inground

Inground, 12W LED, 3000K, 120V

Inground, 12W LED, 3000K, 120V - 100 lm/W

The revolutionary i1.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i1.5 reinforces HADCO's position as the leader in landscape lighting.

Product data

| General information | | Initial performance (IEC compliant) | |
|-------------------------------|-------------------|-------------------------------------|--------------------------------|
| Lamp Source Code | LED | Luminaire Lumens | 800 |
| Lamp Watts | 17 | Efficacy | 100 lm/W |
| Number of Lamps | 1 | | |
| Colour Temperature | 3000 K | Product data | |
| CRI | 80 | Order product name | I15 INGROUND, LED |
| Photometric Distribution Type | Medium | Order code | I15NFLW |
| Mounting | In Ground | Numerator - Quantity Per Pack | 1 |
| Number Of Pieces | 1 | Numerator - Packs per outer box | 1 |
| | | Material Nr. (12NC) | 912400122736 |
| | | Net Weight (Piece) | 0.010 kg |
| | | Catalog Number | I15NFLW |
| | | Catalog Number Description | Inground, 12W LED, 3000K, 120V |
| Operating and electrical | | | |
| Voltages | 120 V | | |
| Luminaire Input Watts | 17 | | |
| Conduit Connection | 7/8 inch knockout | | |
| Mechanical and housing | | | |
| Enclosure | Metal and Plastic | | |