



# i25 Inground

## I25 INGROUND,100W INCAND

Inground, 100W INC, Natural Brass, 120V

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i2.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

### Product data

|                                 |                          |                                 |   |       |
|---------------------------------|--------------------------|---------------------------------|---|-------|
| <b>General Information</b>      |                          | <b>Order code</b>               |   | I25-N |
| Lamp Source Code                | Incandescent             | Numerator - Quantity Per Pack   | 1                                       |       |
| Lamp Watts                      | 100                      | Numerator - Packs per outer box | 1                                       |       |
| Number of Lamps                 | 1                        | Material Nr. (12NC)             | 912400122756                            |       |
| Mounting                        | In Ground                | Net Weight (Piece)              | 12.840 kg                               |       |
| <b>Operating and Electrical</b> |                          | Commercial Code                 | I25-N                                   |       |
| Voltages                        | 120 V                    | Catalog Number Description      | Inground, 100W INC, Natural Brass, 120V |       |
| Luminaire Input Watts           | 100                      | Quick Ship                      | -                                       |       |
| <b>Product Data</b>             |                          |                                 |   |       |
| Order product name              | I25 INGROUND,100W INCAND |                                 |   |       |