



# IL Composite Inground

## INGROUND,COMPOSITE RING,12V75W

Inground, Bronze, 75W PAR 36, 12V

The IL Composite Inground luminaire is for low voltage landscape lighting. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. It is available in halogen, incandescent and LED. The optical assembly has a clear convex, tempered soda-lime glass and 358° rotation without interruption of the beam pattern.

### Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	75
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	75
Product Data	
Order product name	INGROUND,COMPOSITE RING,12V75W

EAN/UPC - Product	783352007049
Order code	IL136-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400123064
Net Weight (Piece)	0.001 kg
Commercial Code	IL136-H
Catalog Number Description	Inground, Bronze, 75W PAR 36, 12V
Quick Ship	-