



i2 Inground

INGR W/GRD/TRANS,12V,75W,PAR36

Inground, w/ Cast Bronze Rock Guard, Natural Brass, 75W PAR 36, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information		Order code IT236G-N	
Lamp Source Code	Quartz	Local order code	-
Lamp Watts	75	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	In Ground	Material Nr. (12NC)	912400123115
Operating and Electrical		Net Weight (Piece)	0.010 kg
Voltages	120 V	Commercial Code	IT236G-N
Luminaire Input Watts	75	Catalog Number Description	Inground, w/ Cast Bronze Rock Guard, Natural Brass, 75W PAR 36, 120V
Product Data		Quick Ship	-
Order product name	INGR W/GRD/TRANS,12V,75W,PAR36		
EAN/UPC - Product	783352021243		