



RFL1 Steplight

Step Light, Aluminum, Recessed, Black, 12W S-8 (93), 12V

Step Light, Aluminum, Recessed, Black, 12W S-8 (93), 12V

RFL1 step light is a low voltage for wall applications. The die-cast aluminum faceplate includes a galvanized steel, single gang recessed box with stainless steel fasteners. A frosted tempered glass lens is included and lamping requires a 12W maximum S-8 (93) lamp.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Incandescent	Order code	RFL1-A
Lamp Watts	28	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	2
Mounting	Recessed	Material Nr. (12NC)	912400125951
Operating and Electrical		Net Weight (Piece)	0.010 kg
Voltages	12 V	Catalog Number	RFL1-A
Luminaire Input Watts	28	Catalog Number Description	Step Light, Aluminum, Recessed, Black, 12W S-8 (93), 12V
Product Data			
Order product name	STEPLYTE, RECESSED, 12V, 12W, W/93		