



# RSC2 Step Light LED

LVR BRICKLYTE,120V,40W,T10

Step Light, Aluminum, Black, 40W T10, 120V

The RSC2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. It is available with a die-cast aluminum and bronze construction with low copper to resist corrosion. The cast bronze louver is natural cast bronze with frosted tempered glass. The die-cast copper-free aluminum louver has a 45° cutoff with frosted tempered glass with silicone gasketing. Available in three colors plus natural bronze. Symmetric Reflector is precision formed with a white reflective coating. The cast louver offers lower light levels with cut-off for lighting stairways or general lighting where shielding of the light source is more important than high light levels.

## Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	28
Number of Lamps	1
Photometric Distribution Type	General Diffuse
Mounting	Recessed
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	28
Product Data	
Order product name	LVR BRICKLYTE,120V,40W,T10

EAN/UPC - Product	783352010766
Order code	RSC2AK5IE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400126253
Net Weight (Piece)	0.001 kg
Commercial Code	RSC2AK5IE
Catalog Number Description	Step Light, Aluminum, Black, 40W T10, 120V
Quick Ship	Spec Smart (10 Days) USA