



RSC2 Step Light LED

Step Light, Aluminum, Black, 40W T10, 120V

Step Light, Aluminum, Black, 40W T10, 120V

The RSC2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. It is available with a die-cast aluminum and bronze construction with low copper to resist corrosion. The cast bronze louver is natural cast bronze with frosted tempered glass. The die-cast copper-free aluminum louver has a 45° cutoff with frosted tempered glass with silicone gasketing. Available in three colors plus natural bronze. Symmetric Reflector is precision formed with a white reflective coating. The cast louver offers lower light levels with cut-off for lighting stairways or general lighting where shielding of the light source is more important than high light levels.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Incandescent	EAN/UPC - Product	783352010766
Lamp Watts	28	Order code	RSC2AK5IE
Number of Lamps	1	Numerator - Quantity Per Pack	1
Photometric Distribution Type	General Diffuse	Numerator - Packs per outer box	1
Mounting	Recessed	Material Nr. (12NC)	912400126253
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120 V	Catalog Number	RSC2AK5IE
Luminaire Input Watts	28	Catalog Number Description	Step Light, Aluminum, Black, 40W T10, 120V
Product Data			
Order product name	LVR BRICKLYTE,120V,40W,T10		