



RSC2 Step Light LED

LVR BRICKLYTE,120V,13W,PLC13

Step Light, Aluminum, Bronze, 13W PLC13, 120V

The RSC2 is a line voltage step light perfect for high pedestrian traffic and plant life applications. It is available in standard sources including CFL along with high brightness LED sources. It is available with a die-cast aluminum and bronze construction with low copper to resist corrosion. The cast bronze louver is natural cast bronze with frosted tempered glass. The die-cast copper-free aluminum louver has a 45° cutoff with frosted tempered glass with silicone gasketing. Available in three colors plus natural bronze. Symmetric Reflector is precision formed with a white reflective coating. The cast louver offers lower light levels with cut-off for lighting stairways or general lighting where shielding of the light source is more important than high light levels.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Compact Fluorescent	Order code	RSC2HK5F13E
Lamp Watts	28	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Photometric Distribution Type	General Diffuse	Material Nr. (12NC)	912400126284
Mounting	Recessed	Net Weight (Piece)	0.001 kg
Operating and Electrical		Commercial Code	RSC2HK5F13E
Voltages	120 V	Catalog Number Description	Step Light, Aluminum, Bronze, 13W PLC13, 120V
Luminaire Input Watts	28	Quick Ship	Spec Smart (10 Days) USA
Product Data			
Order product name	LVR BRICKLYTE,120V,13W,PLC13		