



WAM1/WBM1 Mini Floodlight

T3 120V MINI FLOOD W/SHOURED

Floodlight, Aluminum w/ Shroud, Bronze, 75W T3, 120V

The WAM1/WBM1 landscape flood light is a line voltage luminaire used for general illumination. It's constructed of die-cast aluminum with silicone gasketing. A fully-adjustable swivel arm with vibration-proof locking teeth is used for mounting. Optics include a Clear tempered glass lens or frosted tempered glass lens with 75W T3 or LED source. The LED lamp source delivers 50,000 hours of operating life, has a CCT of 3,000K or 4,000K and a CRI of 80.

Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	75
Number of Lamps	1
Mounting	NPT/NPS
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	75
Initial Performance (IEC Compliant)	
Luminaire Lumens	9120

Product Data	
Order product name	T3 120V MINI FLOOD W/SHOURED
EAN/UPC - Product	783352014566
Order code	WAM1-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400129265
Net Weight (Piece)	0.680 kg
Commercial Code	WAM1-H
Catalog Number Description	Floodlight, Aluminum w/ Shroud, Bronze, 75W T3, 120V
Quick Ship	Service Smart (2 Days) USA