

iColor Flex MX gen2

iColor Flex MX gen2, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing

iColor Flex MX gen2, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative mid/low-resolution video displays, iColor Flex MX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex MX gen2 node is individually controllable, providing ultimate flexibility of design.

Product data

General information		Mechanical and housing	
Number of light sources	50 [50 pcs]	Housing material	Polycarbonate
Lamp family code	LED-MD [LED Multi-die]	Optical cover/lens material	Polycarbonate
Light source colour	RGB	Colour	Black
Light source replaceable	Yes	Approval and application	
Driver included	No	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Optical cover/lens type	TSDM4 [Transparent dome 4 inch separated]	Initial performance (IEC compliant)	
Luminaire light beam spread	165°	Initial LED luminaire efficacy	8 lm/W
CE mark	CE mark	Initial input power	0.5 W
Operating and electrical		Over time performance (IEC compliant)	
Input Voltage	7.5 V	Lumen Maintenance 50% at 25 °C Calculated	60000
Controls and dimming		Lumen Maintenance 50% at 25 °C Reported	60000
Dimmable	Yes	Lumen Maintenance 50% at 50 °C Calculated	60000
		Lumen Maintenance 50% at 50 °C Reported	60000

iColor Flex MX gen2

Lumen Maintenance 70% at 25 °C Calculated	60000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	60000
Lumen Maintenance 70% at 50 °C Reported	60000

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product data

Full product code	871829162292599
Order product name	BGC494 50 RGB TSDM4 BK
EAN/UPC – product	8718291622925

Order code	101-000076-02
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130016
Net Weight (Piece)	0.717 kg
Commercial Code	101-000076-02
Catalogue number description	iColor Flex MX gen2, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing

IP 66

Dimensional drawing



BGC494 50 RGB TSDM4 BK

