



# iColor Flex MX gen2

## iColor Flex MX gen2, Clear Dome Lens, Black Housing, 4 in On-Center Node Spacing

iColor Flex MX gen2, Clear Dome Lens, Black Housing, 4 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative mid/low-resolution video displays, iColor Flex MX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex MX gen2 node is individually controllable, providing ultimate flexibility of design.

### Product data

General information	
Number of light sources	50 [ 50 pcs]
Lamp family code	LED-MD [ LED Multi-die]
Lamp colour code	RGB
Light source replaceable	Yes
Driver included	No
Optical cover/lens type	CLDM4 [ Clear dome 4 inch separated]
Luminaire light beam spread	105°
CE mark	CE mark
Operating and electrical	
Input Voltage	7.5 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing material	Polycarbonate

Optical cover/lens material	Polycarbonate
Colour	Black
Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Initial performance (IEC compliant)	
Initial LED luminaire efficacy	12 lm/W
Initial input power	0.5 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	60000
Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	60000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	60000
Lumen Maintenance 70% at 25 °C Reported	60000


## iColor Flex MX gen2

Lumen Maintenance 70% at 50 °C Calculated	60000
Lumen Maintenance 70% at 50 °C Reported	60000
<b>Application conditions</b>	
Ambient temperature range	-40 to +50 °C
<b>Product data</b>	
Full product code	871829162296399
Order product name	BGC494 50 RGB CLDM4 BK
EAN/UPC – product	8718291622963
Order code	101-000076-06


SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130020
Net Weight (Piece)	0.692 kg
Commercial Code	101-000076-06
Commercial Code	iColor Flex MX gen2, Clear Dome Lens, Black Housing, 4 in On-Center Node Spacing

IP 66

### Dimensional drawing



BGC494 50 RGB CLDM4 BK



BGC494 50 RGB CLDM4 BK

