



iColor Flex LMX gen2

BGC495 50 RGB TSDM4 WH

iColor Flex LMX gen2, Translucent Dome Lens, White Housing, 4 in On-Center Node Spacing

When designers need high-brightness RGB direct-view accent lighting, or need to design creative low-resolution video displays, iColor Flex LMX gen2 provides flexible strands of large high-intensity LED nodes. Each Flex LMX gen2 node is individually controllable, providing ultimate flexibility of design.

Product data

General Information		Controls and Dimming	
Number of light sources	50 [50 pcs]	Dimmable	Yes
Lamp family code	LED-MD [LED Multi-die]	Mechanical and Housing	
Lamp colour code	RGB	Housing material	Polycarbonate
Light source replaceable	Yes	Optical cover/lens material	Polycarbonate
Driver included	No	Colour	White
Optical cover/lens type	TSDM4 [Transparent dome 4 inch separated]	Approval and Application	
Luminaire light beam spread	165°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
CE mark	CE mark	Initial Performance (IEC Compliant)	
Light Technical		Initial luminous flux (system flux)	13 lm
Luminous intensity (peak value) on beam axis per node	2.2 cd	Initial LED luminaire efficacy	13 lm/W
Operating and Electrical		Initial input power	1 W
Input Voltage	24 V	Over Time Performance (IEC Compliant)	
		Lumen Maintenance 50% at 25 °C Calculated	100000

iColor Flex LMX gen2

Lumen Maintenance 50% at 25 °C Reported	60000
Lumen Maintenance 50% at 50 °C Calculated	100000
Lumen Maintenance 50% at 50 °C Reported	60000
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000

Application Conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Product Data

Full product code	871829162312099
Order product name	BGC495 50 RGB TSDM4 WH

EAN/UPC – product	8718291623120
Order code	101-000077-06
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130028
SAP net weight (piece)	0.980 kg
Commercial Code	101-000077-06
Commercial Code	iColor Flex LMX gen2, Translucent Dome Lens, White Housing, 4 in On- Center Node Spacing



Dimensional drawing



iColor Flex LMX gen2

