



Vaya Linear MP

BCP424 50 RGB L310 CE CQC

Vaya Linear MP is a reliable and cost-effective LED wall grazing luminaire for both interior and exterior use that minimizes initial investment, while offering exceptional flexibility to create eye-catching wall washing and wall grazing effects. A wide range of color and CCT options, in either static on/off or with dynamic color control, adjustable mounting brackets, wide or elliptical beam angles offer a comprehensive toolbox for your facade lighting needs. The discreet design with integrated power supply and waterproof connectors makes wiring simple, fast and reliable.

Product data

General Information		Mechanical and Housing	
Lamp family code	LED-HB [LED High Brightness]	Housing Material	Aluminum extruded
Beam angle of light source	50 °	Optic material	Glass
Light source color	Red, green and blue	Optical cover/lens material	Tempered glass
Light source replaceable	No	Optical cover/lens shape	Flat
Driver included	Yes	Optical cover/lens finish	Clear
Optical cover/lens type	Clear glass	Length	310 mm
CE mark	CE mark	Color	Dark gray
UL mark	-	Approval and Application	
CQC mark	CQC-mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Lifetime to 70% luminous flux	60000 h	Mech. impact protection code	IK06 [1 J]
PSE mark	No	Vibration Standard	Complies with ANSI C136.31
Operating and Electrical		Vibration Rating	Complies with ANSI C136.31
Input Voltage	100 to 277 V	Initial Performance (IEC Compliant)	
Input Frequency	50 to 60 Hz	Initial luminous flux (system flux)	477 lm
Controls and Dimming		Initial LED luminaire efficacy	35.1 lm/W
Dimmable	Yes	Init. Corr. Color Temperature	- K

Vaya Linear MP

Initial input power	18 W
---------------------	------


Over Time Performance (IEC Compliant)	
Lumen Maintenance 50% at 25°C Calculated	100000
Lumen Maintenance 50% at 25°C Reported	36000
Lumen Maintenance 50% at 40°C Calculated	63000
Lumen Maintenance 50% at 40°C Reported	36000
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	36000
Lumen Maintenance 70% at 40°C Calculated	29000
Lumen Maintenance 70% at 40°C Reported	29000

Application Conditions	
Ambient temperature range	-40 to +40 °C

Product Data	
Full product code	871829162563699
Order product name	BCP424 50 RGB L310 CE CQC
EAN/UPC - Product	8718291625636
Order code	912400130064
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	912400130064
Net Weight (Piece)	1.420 kg



Dimensional drawing



Vaya

