



# Vaya Linear MP

## BCP426 50 BL L310 CE

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colorful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

### Product data

| General Information           |                               |
|-------------------------------|-------------------------------|
| Lamp family code              | LED-HB [ LED High Brightness] |
| Beam angle of light source    | 50 °                          |
| Light source colour           | Blue                          |
| Light source replaceable      | No                            |
| Driver included               | Yes                           |
| Optical cover/lens type       | GC [ Clear glass]             |
| CE mark                       | CE mark                       |
| UL mark                       | -                             |
| CQC mark                      | -                             |
| Lifetime to 70% luminous flux | 60000 h                       |
| PSE mark                      | PSE mark                      |
| Operating and Electrical      |                               |
| Input voltage                 | 100 to 277 V                  |
| Input frequency               | 50 to 60 Hz                   |
| Controls and Dimming          |                               |
| Dimmable                      | No                            |
| Mechanical and Housing        |                               |
| Housing material              | Aluminum extruded             |

|                             |                |
|-----------------------------|----------------|
| Optic material              | Glass          |
| Optical cover/lens material | Tempered glass |
| Optical cover/lens shape    | Flat           |
| Optical cover/lens finish   | Clear          |
| Length                      | 310 mm         |
| Colour                      | Dark gray      |

| Approval and Application     |   |
|------------------------------|---|
| Ingress protection code      | IP66 [ Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [ 1 J]                                   |

| Initial Performance (IEC Compliant) |     |
|-------------------------------------|-----|
| Init. Corr. colour temperature      | - K |

| Application Conditions    |               |
|---------------------------|---------------|
| Ambient temperature range | -40 to +40 °C |


| Product Data       |                      |
|--------------------|----------------------|
| Full product code  | 871829162631299      |
| Order product name | BCP426 50 BL L310 CE |
| EAN/UPC – product  | 8718291626312        |
| Order code         | 62631299             |

Vaya Linear MP


|                                 |              |
|---------------------------------|--------------|
| Numerator – quantity per pack   | 1            |
| Numerator – packs per outer box | 4            |
| Material no. (12NC)             | 912400130076 |
| Net weight (piece)              | 1.420 kg     |



Dimensional drawing



Vaya



Vaya

