



Vaya Linear MP

BCP425 10x50 4000 L1210 CE

Vaya Linear MP is a reliable and cost-effective LED lighting fixture designed for fixed or dynamic colourful lighting effects. Offering a choice of wide or elliptical beams, Vaya Linear MP is ideal for wall washing and grazing applications. Integrated power and unified power and data connectors make installation fast, easy and reliable.

Product data

General Information			
Lamp family code	LED-HB [LED High Brightness]	Optic material	Glass
Beam angle of light source	10 x 50 °	Optical cover/lens material	Tempered glass
Light source colour	Cool white	Optical cover/lens shape	Flat
Light source replaceable	No	Optical cover/lens finish	Clear
Driver included	Yes	Length	1210 mm
Optical cover/lens type	GC [Clear glass]	Colour	Dark Grey
CE mark	CE mark	Approval and Application	
UL mark	No	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
CQC mark	-	Mech. impact protection code	IK06 [1 J]
Lifetime to 70% luminous flux	60000 h	Vibration standard	Complies with ANSI C136.31
PSE mark	PSE mark		Complies with ANSI C136.31
Operating and Electrical		Initial Performance (IEC Compliant)	
Input voltage	100 to 277 V	Initial luminous flux	3375 lm
Input frequency	50 to 60 Hz	Initial luminous flux at color temperature of 4000 K	3375 lm
Controls and Dimming		Initial LED luminaire efficacy	59 lm/W
Dimmable	Yes	Init. Corr. colour temperature	4000 K
Mechanical and Housing		Init. colour rendering index	83
Housing material	Extruded aluminium		


Vaya Linear MP

Initial input power	60 W
Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25°C Calculated	100000
Lumen Maintenance 70% at 25°C Reported	60000
Lumen Maintenance 70% at 40°C Calculated	100000
Lumen Maintenance 70% at 40°C Reported	60000
Lumen Maintenance 80% at 25°C Reported	60000
Lumen Maintenance 80% at 40°C Calculated	100000
Lumen Maintenance 80% at 40°C Reported	60000
Lumen Maintenance 80% at 50°C Calculated	100000
Lumen Maintenance 90% at 25°C Calculated	62000
Lumen Maintenance 90% at 25°C Reported	60000
Lumen Maintenance 90% at 40°C Calculated	62000
Lumen Maintenance 90% at 40°C Reported	60000


Application Conditions	
Ambient temperature range	-40 to +40 °C
Product Data	
Full product code	871829162574299
Order product name	BCP425 10x50 4000 L1210 CE
EAN/UPC – product	8718291625742
Order code	62574299
Numerator – quantity per pack	1
Numerator – packs per outer box	4
Material no. (12NC)	912400130124
Net weight (piece)	3.760 kg



Dimensional drawing



Vaya



Vaya

