



# eW Flex Micro

## eW Flex Micro, 2700 K, Clear Dome Lens, White Housing, 12 in On-Center Node Spacing

eW Flex Micro, 2700 K, Clear Dome Lens, White Housing, 12 in On-Center Node Spacing

eW Flex Micro is a versatile strand of small, individually controllable white- light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Micro can also be used to light tight alcove spaces and signage.

### Product data

<b>General information</b>		<b>Luminance per node</b>	
Number of light sources	50 [ 50 pcs]	25.7	
Lamp family code	LED-MD [ LED Multi-die]	<b>Operating and electrical</b>	
Light source colour	Warm white	<b>Input Voltage</b>	
Light source replaceable	No	24 V	
Driver included	Yes	<b>Controls and dimming</b>	
Optic type	WB [ Wide beam]	<b>Dimmable</b>	
Optical cover/lens type	CLDM12 [ Clear dome 12 inch separated]	Yes	
CE mark	CE mark	<b>Mechanical and housing</b>	
ENEC mark	-	<b>Housing material</b>	
UL mark	UL and cUL mark	Polycarbonate	
Product recyclability	100%	<b>Optic material</b>	
EU RoHS compliant	No	Polycarbonate	
<b>Light technical</b>		<b>Colour</b>	
On-axis intensity in candela	10.1	White	
		<b>Approval and application</b>	
		<b>Ingress protection code</b>	
		IP66 [ Dust penetration-protected, jet-proof]	
		<b>Mech. impact protection code</b>	
		IK09 [ 10 J]	


eW Flex Micro

FCC mark	FCC Class A
Initial performance (IEC compliant)	
Init. Corr. Colour Temperature	2700 K
Initial input power	25 W
Over time performance (IEC compliant)	
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Calculated	90000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	61000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	38000
Lumen Maintenance 90% at 25 °C Reported	38000
Lumen Maintenance 90% at 50 °C Calculated	27000
Lumen Maintenance 90% at 50 °C Reported	27000


Application conditions	
Ambient temperature range	-30 to +50 °C
Product data	
Full product code	871829163901599
Order product name	BGC482 50 2700K CLDM12 WH
EAN/UPC – product	8718291639015
Order code	500-000011-04
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130448
Net Weight (Piece)	0.983 kg
Commercial Code	500-000011-04
Catalogue number description	eW Flex Micro, 2700 K, Clear Dome Lens, White Housing, 12 in On-Center Node Spacing



Dimensional drawing



BGC482 50 2700K CLDM12 WH



BGC482 50 2700K CLDM12 WH

