



# eW Flex Micro

## eW Flex Micro, 6500 K, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing

eW Flex Micro, 6500 K, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing

eW Flex Micro is a versatile strand of small, individually controllable white- light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Micro can also be used to light tight alcove spaces and signage.

### Product data

General information		Operating and electrical	
Number of light sources	50 [ 50 pcs]	Input Voltage	24 V
Lamp family code	LED-MD [ LED Multi-die]	Controls and dimming	
Light source colour	Cool white	Dimmable	Yes
Light source replaceable	No	Mechanical and housing	
Driver included	Yes	Housing material	Polycarbonate
Optic type	WB [ Wide beam]	Optic material	Polycarbonate
Optical cover/lens type	TSDM4 [ Transparent dome 4 inch separated]	Colour	Black
CE mark	CE mark	Approval and application	
ENEC mark	-	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
UL mark	UL and cUL mark	Mech. impact protection code	IK09 [ 10 J]
Product recyclability	100%		
EU RoHS compliant	No		


eW Flex Micro

Initial performance (IEC compliant)	
Init. Corr. Colour Temperature	6500 K
Initial input power	25 W
Over time performance (IEC compliant)	
Lumen Maintenance 70% at 25 °C Calculated	100000
Lumen Maintenance 70% at 25 °C Reported	60000
Lumen Maintenance 70% at 50 °C Calculated	100000
Lumen Maintenance 70% at 50 °C Reported	60000
Lumen Maintenance 80% at 25 °C Calculated	90000
Lumen Maintenance 80% at 25 °C Reported	60000
Lumen Maintenance 80% at 50 °C Calculated	61000
Lumen Maintenance 80% at 50 °C Reported	60000
Lumen Maintenance 90% at 25 °C Calculated	38000
Lumen Maintenance 90% at 25 °C Reported	38000
Lumen Maintenance 90% at 50 °C Calculated	27000
Lumen Maintenance 90% at 50 °C Reported	27000
Application conditions	
Ambient temperature range	-30 to +50 °C

Product data	
Full product code	871829163940499
Order product name	BGC482 50 6500K TSDM4 BK
EAN/UPC – product	8718291639404
Order code	500-000011-43
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	912400130487
Net Weight (Piece)	0.183 kg
Commercial Code	500-000011-43
Catalogue number description	eW Flex Micro, 6500 K, Translucent Dome Lens, Black Housing, 4 in On-Center Node Spacing



Dimensional drawing



BGC482 50 6500K TSDM4 BK

