



eW Flex Compact

eW Flex Compact, 2700 K, Clear Flat Lens, White Housing, 4 in on-center node spacing

eW Flex Compact, 2700 K, Clear Flat Lens, White Housing, 4 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

Product data

General information		Operating and electrical	
Number of light sources	50 [50 pcs]	Input Voltage	24 V
Lamp family code	LED-MD [LED Multi-die]		
Light source replaceable	No	Controls and dimming	
Driver included	No	Dimmable	Yes
Optical cover/lens type	CLFT4 [Clear flat 4 inch separated]		
CE mark	CE mark	Mechanical and housing	
ENEC mark	-	Housing material	Polycarbonate
UL mark	UL mark	Optic material	Polycarbonate
Product recyclability	100%	Colour	White
EU RoHS compliant	No		
		Approval and application	
Light technical		Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Luminance per node	45127 cd/m²	Mech. impact protection code	IK10 [20 J vandal-resistant]
Luminous intensity (peak value) on beam axis per node	29.8 cd	FCC mark	FCC Class A

eW Flex Compact

Initial performance (IEC compliant)

Init. Corr. Colour Temperature	2700 K
Initial input power	50 W

Over time performance (IEC compliant)

Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product data

Full product code	871829164577199
Order product name	BGC481 50 2700K CLFT4 WH
EAN/UPC – product	8718291645771
Order code	500-000012-00
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130619
Net Weight (Piece)	0.980 kg
Commercial Code	500-000012-00
Catalogue number description	eW Flex Compact, 2700 K, Clear Flat Lens, White Housing, 4 in on-center node spacing

