



# Flex Compact, eW

## eW Flex Compact, 2700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact, 2700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact is a versatile strand of 50 individually controllable LED nodes. The flexible form factor allows dynamic points of white light to be installed across nearly any interior or exterior surface, including walls, ceilings, floors, three-dimensional sculptures, and set pieces. eW Flex Compact can also light tight alcove spaces and signage, and in certain cases, can even display video.

### Product data

General information	
Number of light sources	50 pcs
Lamp family code	LED-MD [ LED Multi-die]
Light source replaceable	No
Driver included	No
Optical cover/lens type	Transparent dome 12 inch separated
CE mark	CE mark
ENEC mark	-
UL mark	UL mark
Product recyclability	100%
EU RoHS compliant	No
Light technical	
Luminance per node	10660 cd/m <sup>2</sup>
Luminous intensity (peak value) on beam axis per node	7 cd

Operating and electrical	
Input Voltage	24 V
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Housing Material	Polycarbonate
Optic material	Polycarbonate
Color	Black
Approval and application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [ 20 J vandal-resistant]
FCC mark	FCC Class A

## Flex Compact, eW

### Initial performance (IEC compliant)

Init. Corr. Color Temperature	2700 K
Initial input power	50 W

### Over time performance (IEC compliant)

Lumen Maintenance 70% at 25°C Calculated	56000
Lumen Maintenance 70% at 25°C Reported	56000
Lumen Maintenance 70% at 50°C Calculated	56000
Lumen Maintenance 70% at 50°C Reported	56000
Lumen Maintenance 80% at 25°C Calculated	37000
Lumen Maintenance 80% at 25°C Reported	37000
Lumen Maintenance 80% at 50°C Calculated	37000
Lumen Maintenance 80% at 50°C Reported	37000
Lumen Maintenance 90% at 25°C Calculated	20000
Lumen Maintenance 90% at 25°C Reported	20000
Lumen Maintenance 90% at 50°C Calculated	20000
Lumen Maintenance 90% at 50°C Reported	20000

### Application conditions

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Product data

Full product code	871829164584999
Order product name	BGC481 50 2700K TSDM12 BK
EAN/UPC - Product	8718291645849
Order code	500-000012-07
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	912400130626
Net Weight (Piece)	1.500 kg
Catalog Number	500-000012-07
Catalog Number Description	eW Flex Compact, 2700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing

