



# eW Flex Compact

## eW Flex Compact, 5700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact, 5700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing

eW Flex Compact is a versatile strand of large, individually controllable white-light LED nodes. The flexible form factor allows dynamic points of white light to be installed across almost any interior or exterior surface, including walls, ceilings, floors, and three-dimensional sculptures. eW Flex Compact can also be used to light tight alcove spaces and signage.

### Product data

General Information		Controls and Dimming	
Number of light sources	50 [ 50 pcs]	Dimmable	Yes
Lamp family code	LED-MD [ LED Multi-die]		
Light source replaceable	No	Mechanical and Housing	
Driver included	No	Housing material	Polycarbonate
Optical cover/lens type	TSDM12 [ Transparent dome 12 inch separated]	Optic material	Polycarbonate
CE mark	CE mark	Colour	Black
ENEC mark	-	Approval and Application	
UL mark	UL mark	Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Product recyclability	100%	Mech. impact protection code	IK10 [ 20 J vandal-resistant]
EU RoHS compliant	No	Initial Performance (IEC Compliant)	
Operating and Electrical		Init. Corr. Colour Temperature	5700 K
Input Voltage	24 V	Initial input power	1 W

eW Flex Compact


Over Time Performance (IEC Compliant)	
Lumen Maintenance 70% at 25 °C Calculated	56000
Lumen Maintenance 70% at 25 °C Reported	56000
Lumen Maintenance 70% at 50 °C Calculated	56000
Lumen Maintenance 70% at 50 °C Reported	56000
Lumen Maintenance 80% at 25 °C Calculated	37000
Lumen Maintenance 80% at 25 °C Reported	37000
Lumen Maintenance 80% at 50 °C Calculated	37000
Lumen Maintenance 80% at 50 °C Reported	37000
Lumen Maintenance 90% at 25 °C Calculated	20000
Lumen Maintenance 90% at 25 °C Reported	20000
Lumen Maintenance 90% at 50 °C Calculated	20000
Lumen Maintenance 90% at 50 °C Reported	20000

Application Conditions	
Ambient temperature range	-40 to +50 °C

Product Data	
Full product code	871829164616799
Order product name	BGC481 50 5700K TS DM12 BK
EAN/UPC – product	8718291646167
Order code	500-000012-39
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400130658
SAP net weight (piece)	1.500 kg
Commercial Code	500-000012-39
Catalogue number description	eW Flex Compact, 5700 K, Translucent Dome Lens, Black Housing, 12 in on-center node spacing



Dimensional drawing



eW Flex SLX

