



# PureStyle IntelliHue Powercore



## PureStyle IntelliHue Powercore, 100° x 100°, 1219 mm (48 in), Wide Beam Angle

PureStyle IntelliHue Powercore, 100° x 100°, 1219 mm (48 in), Wide Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications – from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

### Product data


General information		CRI @ 2,700	
Light source colour	IntelliHue	92.9	
Optic type	WB [ Wide beam]	Operating and electrical	
Optical cover/lens type	PC [ Polycarbonate bowl/cover]	Input Voltage	100 to 277 V
Luminaire light beam spread	100° x 100°	Mechanical and housing	
CE mark	CE mark	Housing material	Extruded aluminium
UL mark	UL and cUL mark	Length	1220 mm
Light technical		Colour	White
Efficacy (lm/W) @ 4,000 K	55 lm/W	Approval and application	
Efficacy (lm/W) @ 2,700 K	55 lm/W	Ingress protection code	IP20 [ Finger-protected]
CRI @ 4,000 K	93.8	Energy Efficiency Class	G
CRI R9 @ 4,000 K	70	FCC mark	FCC Class B

PureStyle IntelliHue Powercore

887772	
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	2860 lm
Initial LED luminaire efficacy at RGB operation	55 lm/W
Initial input power	52 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	72300
Lumen Maintenance 50% at 25 °C Reported	47100
Lumen Maintenance 50% at 50 °C Calculated	72300
Lumen Maintenance 50% at 50 °C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C

Product data	
Full product code	871829139151799
Order product name	SA500X 120X120 INTELLIHUE L1220
EAN/UPC – product	8718291391517
Order code	123-000025-03
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	912400133451
Net Weight (Piece)	1.847 kg
Commercial Code	123-000025-03
Catalogue number description	PureStyle IntelliHue Powercore, 100° x 100°, 1219 mm (48 in), Wide Beam Angle

Dimensional drawing



SA500X 120X120 INTELLIHUE L1220

