



PureStyle Intelligent Colour RGBA Powercore

PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Innovative PureStyle Powercore luminaires bring lighting professionals high output in a compact, easily concealed luminaire. PureStyle delivers exceptionally high-quality light for a wide range of interior applications, from cove to wall-washing to backlighting and beyond. Here are just some of the powerful advantages that PureStyle brings to lighting professionals and their clients.

Product data


General information		Mechanical and housing	
Light source colour	RGBA	Housing material	Aluminum extruded
Optic type	MB [Medium beam]	Length	305 mm
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Colour	White
Luminaire light beam spread	30° x 60°	Approval and application	
CE mark	CE mark	Ingress protection code	IP20 [Finger-protected]
UL mark	UL and cUL mark	Energy Efficiency Class	G
Operating and electrical		FCC mark	FCC Class B
Input Voltage	100 to 277 V		887776

PureStyle Intelligent Colour RGBA Powercore

Initial performance (IEC compliant)	
Initial luminous flux (system flux)	481 lm
Initial LED luminaire efficacy at RGB operation	39 lm/W
Initial input power	13 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C Calculated	72300
Lumen Maintenance 50% at 25 °C Reported	47100
Lumen Maintenance 50% at 50 °C Calculated	72300
Lumen Maintenance 50% at 50 °C Reported	47100
Application conditions	
Ambient temperature range	-20 to +50 °C
Product data	
Full product code	871829139155599

Order product name	SA500X 30X60 RGBA L305
EAN/UPC – product	8718291391555
Order code	123-000026-01
SAP numerator – quantity per pack	1
Numerator – packs per outer box	20
SAP material	912400133455
Net Weight (Piece)	0.485 kg
Commercial Code	123-000026-01
Catalogue number description	PureStyle Intelligent Color Powercore, RGBA, 30° x 60°, 305 mm (12 in), Medium Beam Angle

Dimensional drawing



SA500X 30X60 RGBA L305

